



BURNDY Catalog Number
UPC Number
Description
Status

YA6CLNT6
 7818100602477
 6,SHORT, 6ST,NAR.TONG.
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.17
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.17
Barrel Type	Standard
Thickness	0.09
B Length (in)	0.54
Pad Width (in)	0.29
Strip Length	7/8

General

Number of Holes	1
Product Description	Copper Compression Lug, Narrow Tongue, 1 Hole w/ Inspection Window, 6 AWG, #6 Stud, Short Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	6 AWG
DLO Size (Range)	N/A
Copper Stranded (Range)	6 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	#6
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175