



BURNDY Catalog Number
UPC Number
Description
Status

YA8CLNT6
 7818100343099
 8 STR CU 1-HOLE NAR.TON.
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.08
Barrell Style	Chamfered
Barrel Type	Standard
Thickness	0.09
B Length (in)	0.44
Pad Width (in)	0.29
Strip Length	1/2

General

Number of Holes	1
Product Description	Flex Conductor Standard Barrel Narrow, #8 AWG, 6, 1.08 in L

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	8 AWG

Physical

Type of Plating	Tin - Electro Plated
Color Code	Red
Plated (Yes or No)	Y
Index Number	49
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175