



BURNDY Catalog Number
UPC Number
Description
Status

YAV102TC14
 7818100218422
 HYLUG-OPEN-14/10 STR-(2)
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.84
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.05
B Length (in)	0.38
Pad Width (in)	0.41
E - in	0.62
Strip Length	7/16

General

Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/ Inspection Window, 14 AWG -10 AWG (str)/ 12 AWG-10 AWG (sol), 1/4" Stud, 5/8" Stud Hole Spacing, Short Barrel, Tin - Electro Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	12 AWG-10 AWG
DLO Size (Range)	N/A
Copper Stranded (Range)	14 AWG-10 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Plated (Yes or No)	Y
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday

Phone: 800-346-4175