



BURNDY Catalog Number
UPC Number
Description
Status

YA4CA3
 7818107518000
 4 AL 1-HOLE 5/16
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle Straight
 Strip Length 7/8
 Length (in) 2.25
 Tongue Type Standard
 Bolt Hole Size (in) 0.33
 Thickness 0.12
 B Length (in) 0.88
 Pad Width (in) 0.80

General

Number of Holes 1
 Product Description Aluminum Compression Lug, 1 Hole w/o Inspection Window, 4 AWG, 5/16" Stud, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range) 4 AWG
 Copper Solid Size (Range) N/A
 Copper Stranded (Range) 4 AWG

Physical

Type of Plating Tin - Electro Plated
 Bolt Hole Size 5/16
 Color Code Green
 Plated (Yes or No) Y
 Index Number 375
 Product Material Aluminum

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175