



BURNDY Catalog Number
UPC Number
Description
Status

YA6CL2TC14E2
7818100183477
CU HYDENT 6 STR (2)1/4-
Active

Web Use
BURNDY Product Line

Dimensional

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Straight
2.19
Standard
Chamfered,Skived
0.27
Standard
0.08
0.54
0.45
0.75
5/8

General

Number of Holes

Product Description

2
Copper Compression Lug, 2 Hole
w/ Inspection Window, 6 AWG,
1/4" Stud, 3/4" Stud Hole
Spacing, Short Barrel, Tin - Electro
Plated

Conductor(s)

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

N/A
N/A
N/A
N/A
N/A
6 AWG

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
1/4
Blue
Y
7,374
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Y
Y
Compliant
N
N
UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175