


BURNDY Catalog Number

KA2U

UPC Number

7818103700566

Description

14STR-2STR DUAL RATED

Status

Active

Web Use

BURNDY Product Line

Dimensional

Width (in)	0.50
Length (in)	1.16
Bolt Hole Size (in)	0.25
Thickness	0.10
D - in	0.63
Pad Width (in)	0.51
N (in)	0.31

General

Number of Conductors	1
Number of Holes	1
Product Description	Aluminum Universal Terminal, 1 Hole, 14-2 AWG (Str), 1/4" Stud, 1 Screw, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range)	14 STR- 2 STR
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	14-2

Physical

Installation Torque	50
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	1/4
Plated (Yes or No)	Y
Product Material	Aluminum

Approvals / Certifications

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175