



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA4CL3BOX  
 7818105524388  
 CULUG- 4 STR-SHORT-5/16  
 Active

**Web Use**  
 BURNDY Product Line

#### Dimensional

|                     |                  |
|---------------------|------------------|
| Tongue Angle        | Straight         |
| Length (in)         | 1.79             |
| Tongue Type         | Standard         |
| Barrell Style       | Chamfered,Skived |
| Bolt Hole Size (in) | 0.33             |
| Barrel Type         | Standard         |
| Thickness           | 0.08             |
| B Length (in)       | 0.81             |
| Pad Width (in)      | 0.50             |
| Strip Length        | 7/8              |

#### General

|                     |                                                                                                                                                                              |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Number of Holes     | 1                                                                                                                                                                            |
| Product Description | CU Compression Terminal Code<br>Conductor, Beveled Entry, 1<br>Hole/W/InspWindow,<br>#4AWG(Code) 40(Navy), 600V-<br>35kV, 5/16" Stud, Standard<br>Barrel, Electro-Tin Plated |

#### Conductor(s)

|                             |       |
|-----------------------------|-------|
| Flex (Class G) Size - Range | N/A   |
| Flex (Class H) Size - Range | N/A   |
| Flex (Class I) Size - Range | N/A   |
| Copper Solid Size (Range)   | N/A   |
| DLO Size (Range)            | N/A   |
| Copper Stranded (Range)     | 4 AWG |

#### Physical

|                    |                      |
|--------------------|----------------------|
| Type of Plating    | Tin - Electro Plated |
| Bolt Hole Size     | 5/16                 |
| Color Code         | Gray                 |
| Plated (Yes or No) | Y                    |
| Index Number       | 8                    |
| Product Material   | Copper               |

#### Approvals / Certifications

|                 |           |
|-----------------|-----------|
| UL Listed       | Y         |
| CSA Certified   | Y         |
| ROHS Compatible | Compliant |
| UL Recognized   | N         |
| CULUS           | N         |

#### Documentation

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175