



BURNDY Catalog Number
UPC Number
Description
Status

YAZ8C2TC14FX
7818103243633
CULUG-8FLEX-LONG W/PORT
Active

Web Use
BURNDY Product Line

Dimensional

Tongue Angle	Straight
Strip Length	1
Length (in)	2.33
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.27
Barrel Type	Long
Thickness	0.08
B Length (in)	0.81
Pad Width (in)	0.44
E - in	0.63

General

Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/ Inspection Window, 3 Flex, 1/4" Stud, 5/8" Stud Hole Spacing, Long Barrel, Tin Plated

Conductor(s)

Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	8 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Red
Plated (Yes or No)	Y
Index Number	49
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175