



BURNDY Catalog Number
UPC Number
Description
Status

YAV6CL2TC14FX90
 7818100339755
 6FLEX 2-H 1/4STUD 90
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	90 Degree
Length (in)	1.52
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.08
B Length (in)	0.50
Pad Width (in)	0.48
E - in	0.63
Strip Length	9/16

General

Number of Holes	2
Product Description	Cu Comp Terminal Flex Cond, 2 Hole/W/InspWindow, #6 Weld, 6(61/#24)DLO Flex, #6 AWG Code, 30 Navy, 600 V-35 kV, 1/4" Stud, 0.63" Spacing, 90 Deg Bent, Std bbl

Conductor(s)

Flex (Class G) Size - Range	6 AWG
Flex (Class H) Size - Range	6 AWG
Flex (Class I) Size - Range	6 AWG
Copper Solid Size (Range)	6 AWG
DLO Size (Range)	6 (61/#24) DLO
Copper Stranded (Range)	6 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175