



BURNDY Catalog Number
UPC Number
Description
Status

TP148
 7818107126411
 RING- 16- 14 AWG- VINYL
 Active

Web Use
 BURNDY Product Line

Dimensional	
Max Insulation Diameter	0.18
Length (in)	0.85
Tongue Type	Ring
Thickness	0.03
B Length (in)	0.26
Pad Width (in)	0.31
Strip Length	13/64
Electrical	
Max Voltage Rating	600
General	
Product Description	Copper Terminal, Ring Tongue, 16-14 AWG, #6-#8 Stud, Vinyl Insulated, Tin Plated, Wire strip Length:13/64"
Other	
Bulk Package	BA14E8M
Physical	
Type of Plating	Tin
Connector Type	Terminal
Color Code	Blue
Insulation Type	Vinyl
Plated (Yes or No)	Y
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467
Conductor(s)	
Copper Solid Size (Range)	16 AWG-14 AWG
Copper Stranded (Range)	16 AWG-14 AWG
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175