



BURNDY Catalog Number	YA4CL2TC1490
UPC Number	7818101099399
Description	CULUG-4STR-1/4X5/8-90DEG
Status	Active

Web Use
BURNDY Product Line

Dimensional	
Tongue Angle	90 Degree
Length (in)	1.53
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.09
B Length (in)	0.81
Pad Width (in)	0.50
E - in	0.62
Strip Length	7/8
General	
Number of Holes	2
Product Description	Cu code conductor std barrel, 2 Holes/W/insp W, #4AWG, 600V-35kV, 1/4" stud, Tin plated, Grey, 8 or 346 Index , UL Listed 90 Deg C
Conductor(s)	
Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	4 AWG
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Gray
Plated (Yes or No)	Y
Index Number	8,346
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175