



BURNDY Catalog Number
UPC Number
Description
Status

YA6C2TC14E2
 7818100197266
 CU HYLUG 6STR 2 HOLE 1/
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	2.78
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.08
B Length (in)	1.12
Pad Width (in)	0.45
E - in	0.75
Strip Length	1-3/16

General

Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/o Inspection Window, 6 AWG, 1/4" Stud, 3/4" Stud Hole Spacing, Long Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	6 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7,374
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175