



BURNDY Catalog Number
UPC Number
Description
Status

YA6C2TC38
 7818100191600
 CU HYDENT 6 STR-(2) 3/8
 Active

Web Use
 BURNDY Product Line

Tongue Angle
 Length (in)
 Tongue Type
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 E - in
 Strip Length

Dimensional

Straight
 3.22
 Standard
 Chamfered,Skived
 0.39
 Standard
 0.06
 1.12
 0.58
 1.00
 1-3/16

Number of Holes
 Product Description

General

2
 Copper Compression Lug, 2 Hole
 w/o Inspection Window, 6 AWG,
 3/8" Stud, 3/8" Stud Hole
 Spacing, Long Barrel, Tin Plated

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

Conductor(s)

N/A
 N/A
 N/A
 N/A
 N/A
 N/A
 6 AWG

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin - Electro Plated
 3/8
 Blue
 Y
 7,374
 Copper

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications

Y
 Y
 Compliant
 N
 N
 UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175