



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA8C2TC14  
 7818100196966  
 CUHYLUG #8 2HOLE 1/4 STUD TEL  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Tongue Angle	Straight
Length (in)	2.33
Tongue Type	Standard
Barrell Style	Chamfered
Barrel Type	Long
Thickness	0.08
B Length (in)	0.81
Pad Width (in)	0.44
E - in	0.62
Strip Length	7/8

**General**

Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/o Inspection Window, 8 AWG/6 AWG, 1/4" Stud, 5/8" Stud Hole Spacing, Long Barrel, Tin Plated

**Conductor(s)**

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	8 AWG
DLO Size (Range)	N/A
Copper Stranded (Range)	8 AWG

**Physical**

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Red
Plated (Yes or No)	Y
Index Number	49
Product Material	Copper

**Approvals / Certifications**

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175