



BURNDY Catalog Number
UPC Number

Description
Status

Web Use
BURNDY Product Line

YAZ6C2TC14E1
7818102275966
CULUG- 6AWG-LONG
W/PORT,1/4STUD E1
Active

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Dimensional

Straight
3.03
Standard
Skived
Long
0.08
1.12
0.45
1.00
1-3/16

Number of Holes

General

2
Cu Comp Terminal Code Cond, Bvl
Entry, 2 Hole/W/InspWindow, #6
AWG Code, 30 Navy, 600 V-35
kV, 1/4" Stud, 1.00" Spacing, Lng
bbl, Blue, 7 or 374 Index

Product Description

Conductor(s)

Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

N/A
30 (19) Navy
6 AWG

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
1/4
Blue
Y
7,374
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175