



BURNDY Catalog Number
UPC Number

YAZ4C2TC14E2
 7818102276400
 CULUG- 4AWG-LONG
 W/PORT,1/4STUD E2
 Active

Description
Status

Web Use
 BURNDY Product Line

Tongue Angle
 Length (in)
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 E - in
 Strip Length

Dimensional

Straight
 2.80
 Skived
 0.27
 Long
 0.09
 1.12
 0.50
 0.75
 1-3/16

Number of Holes

General

2
 Cu Comp Terminal Code Cond, Bvl
 Entry, 2 Hole/W/InspWindow, #4
 AWG Code, 40 Navy, 600 V-35
 kV, 1/4" Stud, 0.75" Spacing, Lng
 bbl, Gray, 8 or 346 Index

Product Description

Conductor(s)

Copper Solid Size (Range)
 Navy Cable Size (Range)
 Copper Stranded (Range)

N/A
 40 (19) Navy
 4 AWG

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin - Electro Plated
 1/4
 Gray
 Y
 8,346
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175