



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA1CL2  
 7818105512644  
 1STR CU 1-HOLE SHORT 1/4  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Tongue Angle	Straight
Length (in)	1.81
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.10
B Length (in)	0.88
Pad Width (in)	0.68
Strip Length	15/16

**General**

Number of Holes	1
Product Description	CU Compression Terminal Code Conductor, Beveled Entry, 1 Hole/W/InspWindow, #1AWG(Code) 75(Navy), 600V- 35kV, 1/4" Stud, Standard Barrel, Electro-Tin Plated

**Conductor(s)**

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	1 AWG

**Physical**

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Green
Plated (Yes or No)	Y
Index Number	375,11
Product Material	Copper

**Approvals / Certifications**

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175