



BURNDY Catalog Number
UPC Number
Description
Status

YA1CL6
 7818105005833
 CU HYLUG- 1 STR-1/2 STUD
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	2.37
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.52
Barrel Type	Standard
Thickness	0.90
B Length (in)	0.88
Pad Width (in)	0.73
Strip Length	15/16

General

Number of Holes	1
Product Description	Cu Tubing Cu Hylug, 1 Hole with Inspection Window, #1 AWG Code,75 Navy, 600V-35kV, 1/2" stud, Standard, Compression, 0.53 in BCD, Green

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	1 AWG

Physical

Type of Plating	Tin - Electro Plated
Color Code	Green
Plated (Yes or No)	Y
Index Number	375,11
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175