



BURNDY Catalog Number
UPC Number
Description
Status

YA3CTC14
 7818100196100
 CU HYLUG 2 SOL-1/4 STUD
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	2.23
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.27
Barrel Type	Long
Thickness	0.09
B Length (in)	1.25
Pad Width (in)	0.55
Strip Length	1-5/16

General

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/o Inspection Window, 3 AWG/2 AWG(Sol), 1/4" Stud, Long Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	2 AWG
DLO Size (Range)	N/A
Copper Stranded (Range)	3 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	White
Plated (Yes or No)	Y
Index Number	9
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175