



BURNDY Catalog Number
UPC Number
Description
Status

YAV25LTC38FX
 7818105182299
 1/0FX 3/8STUD
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.94
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.12
B Length (in)	0.69
Pad Width (in)	0.83
Strip Length	11/16

General

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 1/0 Flex, 3/8" Stud, Short Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	1/0 AWG
Flex (Class H) Size - Range	1/0 AWG
Flex (Class I) Size - Range	1/0 AWG
Copper Solid Size (Range)	N/A
DLO Size (Range)	1/0 (275/#24) DLO
Copper Stranded (Range)	1/0

Physical

Type of Plating	Tin
Bolt Hole Size	3/8
Color Code	Pink
Plated (Yes or No)	Y
Index Number	12
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175