



BURNDY Catalog Number
UPC Number
Description
Status

YAV2CL2TC38FX
7818100222455
CULUG-2FLX-3/8STUDSX1C-C
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Dimensional

Straight
2.82
Standard
Chamfered
0.39
Standard
0.10
0.63
0.68
1.00
11/16

Number of Holes

Product Description

General

2
Copper Compression Lug, 2 Hole
w/ Inspection Window, 2 Flex,
3/8" Stud, 1" Stud Hole Spacing,
Short Barrel, Tin Plated

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

Conductor(s)

2 AWG
2 AWG
2 AWG
2 AWG
3 (125/#24) DLO-2 (150/#24) DLO
2 AWG

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Physical

Tin - Electro Plated
3/8
Brown
Y
10
Copper

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Approvals / Certifications

Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175