



BURNDY Catalog Number
UPC Number
Description
Status

YAZ2C2TC14E1
7818102277255
CULUG- 2STR-LONG W/PORT
Active

Web Use
BURNDY Product Line

Dimensional

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Straight
3.22
Standard
Skived
0.27
Long
0.11
1.25
0.60
1.00
1-5/16

General

Number of Holes

2
Cu Comp Terminal Code Cond, Bvl
Entry, 2 Hole/W/InspWindow, #2
AWG Code, 60 Navy, 600 V-35
kV, 1/4" Stud, 1.00" Spacing, Lng
bbl, Brown, 10 Index

Product Description

Conductor(s)

Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

2 AWG
60 (37) Navy
2 AWG

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
1/4
Brown
Y
10
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible

Y
Y
Compliant

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175