



BURNDY Catalog Number
UPC Number
Description
Status

YA2C2TC38
 7818105035155
 HYLUG-2STR-(2)3/8STUD
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	3.42
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Long
Thickness	0.11
B Length (in)	1.25
Pad Width (in)	0.60
E - in	1.00
Strip Length	1-5/16

General

Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/o Inspection Window, 2 AWG, 3/8" Stud, 1" Stud Hole Spacing, Long Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	2 AWG
DLO Size (Range)	N/A
Copper Stranded (Range)	2 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Brown
Plated (Yes or No)	Y
Index Number	10
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175