



BURNDY Catalog Number
UPC Number
Description
Status

YA2C2TC38E2
7818101595388
CU HYLUG-2STR-3/8X3/4C-C
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Dimensional

Straight
3.17
Chamfered
0.39
Long
0.11
1.25
0.60
0.75
1-5/16

Number of Holes

General

2
Cu Comp Terminal Code Cond, Bvl
Entry, 2 Hole/W/O/InspWindow,
#2 AWG Code, 60 Navy, 600 V-35
kV, 3/8" Stud, 0.75" Spacing, Lng
bbl, Brown, 10 Index

Product Description

Conductor(s)

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

N/A
N/A
N/A
2 AWG
N/A
2 AWG

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
3/8
Brown
Y
10
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Y
Y
Compliant
N
N
UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175