



BURNDY Catalog Number
UPC Number
Description
Status

YAV26LTC516FX
 7818100219966
 CU. COMP. TERM. - 2/0 FL
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle
 Length (in)
 Tongue Type
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 Strip Length

Straight
 1.98
 Standard
 Chamfered
 0.33
 Standard
 0.13
 0.81
 0.93
 13/16

General

Number of Holes
 Product Description

1
 Copper Compression Lug, 1 Hole
 w/ Inspection Window, 2/0 Flex,
 5/16" Stud, Short Barrel, Tin
 Plated

Conductor(s)

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

2/0 AWG
 2/0 AWG
 2/0 AWG
 N/A
 2/0 (375/#24) DLO
 2/0 AWG

Physical

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Tin
 5/16
 Black
 Y
 13
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175