



BURNDY Catalog Number YA26L2TC14
UPC Number 7818100181499
Description 2/0STR 2-H 1/4STUD
Status Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.64
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.12
B Length (in)	0.94
Pad Width (in)	0.83
E - in	0.62
Strip Length	1
General	
Number of Holes	2
Product Description	Cu code conductor std barrel, 2 Holes/W/insp W, 2 Holes/W/insp W, 70mmClass2, 600V-35kV, 1/4" stud, Tin plated, Black, 45 Deg&90 Deg Available
Conductor(s)	
Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	2/0 AWG
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Black
Plated (Yes or No)	Y
Index Number	13
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175