



BURNDY Catalog Number
UPC Number

Description
Status

YAZV252TC14FX
7818102283955
CULUG-1/0 FLX-LONG W/PORT-
1/4STUD, 2HOLE
Active

Web Use
BURNDY Product Line

Dimensional

Tongue Angle	Straight
Strip Length	1-9/16
Length (in)	3.20
Barrell Style	Chamfered, Skived
Bolt Hole Size (in)	0.27
Barrel Type	Long
Thickness	0.12
B Length (in)	1.50
Pad Width (in)	0.83
E - in	0.62

General

Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/ Inspection Window, 1/0 Flex, 1/4" Stud, 5/8" Stud Hole Spacing, Long Barrel, Tin Plated

Conductor(s)

Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	1/0

Physical

Type of Plating	Tin
Bolt Hole Size	1/4
Color Code	Pink
Plated (Yes or No)	Y
Index Number	12,348
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175