



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YAV6CL2TC14FX45  
 7818100228944  
 CUHYLUG- 6FLEX-(2)1/4ST-  
 Active

**Web Use**  
 BURNDY Product Line

Tongue Angle  
 Length (in)  
 Tongue Type  
 Barrell Style  
 Bolt Hole Size (in)  
 Barrel Type  
 Thickness  
 B Length (in)  
 Pad Width (in)  
 E - in  
 Strip Length

**Dimensional**  
 45 Degree  
 2.02  
 Standard  
 Chamfered  
 0.27  
 Standard  
 0.08  
 0.50  
 0.48  
 0.63  
 9/16

Number of Holes

**General**

2  
 Cu Comp Terminal Flex Cond, 2  
 Hole/W/InspWindow, #6 Weld,  
 6(61/#24)DLO Flex, #6 AWG  
 Code, 30 Navy, 600 V-35 kV, 1/4"  
 Stud, 0.63" Spacing, 45 Deg Bent,  
 Std bbl

Product Description

**Conductor(s)**

Flex (Class G) Size - Range  
 Flex (Class H) Size - Range  
 Flex (Class I) Size - Range  
 Copper Solid Size (Range)  
 DLO Size (Range)  
 Copper Stranded (Range)

6 AWG  
 6 AWG  
 6 AWG  
 6 AWG  
 6 (61/#24) DLO  
 6 AWG

Type of Plating  
 Bolt Hole Size  
 Color Code  
 Plated (Yes or No)  
 Index Number  
 Product Material

**Physical**

Tin - Electro Plated  
 1/4  
 Blue  
 Y  
 7  
 Copper

**Approvals / Certifications**

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS

Y  
 Y  
 Compliant  
 N  
 N

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175