



BURNDY Catalog Number
UPC Number
Description
Status

YAV28LTC12FX
7818100217988
HYLUG-4/0 FLEX-1/2 INCH
Active

Web Use
BURNDY Product Line

Dimensional

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
Strip Length

Straight
2.67
Standard
Chamfered
0.52
Standard
0.15
1.03
1.14
1-1/16

General

Number of Holes
Product Description

1
Copper Compression Lug, 1 Hole
w/ Inspection Window, 4/0 Flex,
1/2" Stud, Short Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

4/0 AWG
4/0 AWG
4/0 AWG
N/A
4/0 (550/#24) DLO
4/0 AWG

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin
1/2
Purple
Y
15
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175