



BURNDY Catalog Number
UPC Number
Description
Status

YAV28L2TC38FX
 7818100218733
 4/0 FLEX 2-H 3/8STUD
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	3.43
Tongue Type	Standard
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.15
B Length (in)	1.03
Pad Width (in)	1.14
E - in	1.00
Strip Length	1-1/16

General

Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/ Inspection Window, 4/0 Flex, 3/8" Stud, 1" Stud Hole Spacing, Short Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	4/0 AWG
Flex (Class H) Size - Range	4/0 AWG
Flex (Class I) Size - Range	4/0 AWG
Copper Solid Size (Range)	N/A
DLO Size (Range)	4/0 (550/#24) DLO
Copper Stranded (Range)	4/0 AWG

Physical

Type of Plating	Tin
Bolt Hole Size	3/8
Color Code	Purple
Plated (Yes or No)	Y
Index Number	15
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday

Phone: 800-346-4175