



BURNDY Catalog Number
UPC Number

TN1410
 7818107345688
 RING- 16- 14 AWG-NYLON, 8-10
 STUD
 Active

Description
Status

Web Use
 BURNDY Product Line

Dimensional

Max Insulation Diameter 0.153
 Length (in) 0.89
 Tongue Type Ring
 Pad Width (in) 0.31
 Strip Length 7/32

Electrical

Max Voltage Rating 600

General

Product Description Copper Terminal, Ring Tongue,
 16-14 AWG, #8-#10 Stud, 600
 Volts Max., Nylon Insulated,
 Funnel Entry, Tin Plated

Other

Bulk Package YAES14N8

Physical

Type of Plating Tin - Electro Plated
 Connector Type Terminal
 Color Code Blue
 Insulation Type Nylon
 Plated (Yes or No) Y

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL486

Conductor(s)

Copper Solid Size (Range) 16 AWG-14 AWG
 Copper Stranded (Range) 16 AWG-14 AWG

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175