



BURNDY Catalog Number
UPC Number

Description

Status

YAZ31TC38
7818102402744
CULUG-350KCM-LONG W/PORT-
3/8" STUD
Active

Web Use

BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	3.44
Barrell Style	Skived
Bolt Hole Size (in)	0.39
Barrel Type	Long
Thickness	0.18
B Length (in)	2.00
Pad Width (in)	1.29
Strip Length	2-1/16

General

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 350 kcmil, 3/8" Stud, Long Barrel, Tin Plated

Conductor(s)

Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	350 (91) Navy
Copper Stranded (Range)	350 kcmil

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Red
Plated (Yes or No)	Y
Index Number	18,324
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175