



BURNDY Catalog Number
UPC Number
Description
Status

YAV102TC14E2
7818100218666
10-14AWG 1/4STUD 2-H
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Dimensional

Straight
1.97
Standard
Chamfered
0.27
Standard
0.05
0.38
0.41
0.75
7/16

Number of Holes

General

2
Copper Compression Lug, 2 Hole
w/ Inspection Window, 14 AWG
-10 AWG (str)/ 12 AWG-10 AWG
(sol), 1/4" Stud, 3/4" Stud Hole
Spacing, Short Barrel, Tin - Electro
Plated

Product Description

Conductor(s)

Flex (Class G) Size - Range
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Copper Stranded (Range)

N/A
N/A
N/A
12 AWG-10 AWG
N/A
14 AWG-10 AWG

Type of Plating
Bolt Hole Size
Plated (Yes or No)
Product Material

Physical

Tin - Electro Plated
1/4
Y
Copper

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175