



BURNDY Catalog Number
UPC Number
Description
Status

YAV29L2NTCFX
 7818102822677
 CULUG-4/0FLX-NEMA-YELLOW
 Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	4.62
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Standard
Thickness	0.16
B Length (in)	1.03
Pad Width (in)	1.18
E - in	1.75
Strip Length	1-1/16
General	
Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/ Inspection Window, 4/0 Flex, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel, Electro tin Plated
Conductor(s)	
Flex (Class G) Size - Range	4/0 AWG
Flex (Class H) Size - Range	4/0 AWG
Flex (Class I) Size - Range	4/0 AWG
Copper Solid Size (Range)	N/A
DLO Size (Range)	4/0 (550/#24) DLO
Copper Stranded (Range)	250 kcmil
Physical	
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Yellow
Plated (Yes or No)	Y
Index Number	16
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175