



BURNDY Catalog Number
UPC Number
Description
Status

SP10
7818107100122
SPLICE- 12- 10 AWG-VINYL
Active

Web Use
BURNDY Product Line

Dimensional	
Max Insulation Diameter	.260
Length (in)	1.23
Strip Length	21/64"
Electrical	
Max Voltage Rating	600
General	
Product Description	Copper Splice, 12-10 AWG, 1.23" Splice Length, Vinyl Insulated
Other	
Bulk Package	BS10
Physical	
Type of Plating	Unplated
Connector Type	Splice
Color Code	Yellow
Insulation Type	Vinyl
Plated (Yes or No)	Y
Insulated (Yes or No)	Y
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Conductor(s)	
Aircraft Cable Size (Range)	N/A
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	12 AWG-10 AWG
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175