



BURNDY Catalog Number
UPC Number
Description
Status

YC28C2
7818101157566
3/0-4/0 TO 6-2 CU FIG C
Active

Web Use
BURNDY Product Line

Length (Fraction)

Dimensional
1-1/6

Product Description

General
CU Compression C Shape
Compression Connector, 600 Volts
to 35 Kv, Run: 3/0 Str. - 4/0 Str.,
Tap: 6 Sol. - 2 Str.

Copper Tap Range
Copper Stranded Run (Range)
Copper Solid Tap (Range)
Copper Solid Run Size (Range)

Conductor(s)
6 AWG-2 AWG
3/0 AWG-4/0 AWG
6 AWG-2 AWG
3/0 AWG-4/0 AWG

Type of Plating
Plated (Yes or No)
Product Material

Physical
Unplated
N
Copper

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Approvals / Certifications
Y
Y
Compliant
N
N
UL 486A,UL486B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175