



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

HSC12T300PF  
7818102138033  
25FTX 1/2IN CLR TW HTSHR  
Active

**Web Use**  
BURNDY Product Line

**Dimensional**  
Dimension (Max Before Shrink) 0.50  
Conductor Range #6-2  
Wall Thickness 0.020

**General**  
Heat Shrinkable Cross-Linked Thin Polyolefin Tube, 6 - 2 AWG, 600 V, Shrink Ratio: 2 : 1, Standard reel size: 25 ft

**Conductor(s)**  
Nominal Diameter (Fraction) 1/2

**Physical**  
Shrink Ratio 2:1  
Color Clear

**Approvals / Certifications**  
UL Listed N  
ROHS Compatible Compliant  
UL Recognized N  
CULUS N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175