



BURNDY Catalog Number
UPC Number
Description
Status

YS26A1
7818107571099
BUTT SPLICE, 2.61 IN L
Active

Web Use
BURNDY Product Line

Dimensional

Strip Length 1-3/8
Barrell Style Chamfered
Barrel Type Standard

General

Product Description Aluminum Compression Splice,
2/0 AWG, 2.61" Splice Length,
Long Barrel, Belled End, Tin Plated

Conductor(s)

Aluminum Size (Range) 2/0 AWG
Copper Stranded (Range) 2/0 AWG

Physical

Index Number 297

Approvals / Certifications

UL Listed Y
CSA Certified Y
ROHS Compatible Compliant
UL Recognized N
CULUS N
Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175