



BURNDY Catalog Number
UPC Number
Description
Status

YC10C10
 7818101146055
 12-10 TO 12-10 CU FIG C
 Active

Web Use
 BURNDY Product Line

Length (Fraction)

Dimensional
 3/8

General

Range-taking compression tap connector made of pure copper. For Copper to Copper applications. Designed to be gripped in the jaws or dies of installation tool, then slipped directly over line for easy installation. Also used for deadending.

Product Description

Conductor(s)

Copper Tap Range
 Copper Stranded Run (Range)
 Copper Solid Tap (Range)
 Copper Solid Run Size (Range)

12 AWG-10 AWG
 12 AWG-10 AWG
 12 AWG-10 AWG
 12 AWG-10 AWG

Physical

Type of Plating
 Plated (Yes or No)
 Product Material

Unplated
 N
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

N
 Y
 Compliant
 N
 N
 UL 486A,UL486B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175

