



BURNDY Catalog Number
UPC Number
Description
Status

YGHP34C29
7818102209799
250-500 TO 3/0-250 GRN C
Active

Web Use
BURNDY Product Line

B Length (in)
B Length (Fraction)

Dimensional
0.75
3/4

Product Description

General
Cu Compression Ground Rod
Connector, 3/0 Str - 250 Kcmil,
5/8" - 3/4" Rod Dia

Prefilled (Oxide Inhibitor)

Y

Type of Oxide Inhibitor

Other
Penetrox E

Rated for Direct Burial

Approvals / Certifications

Y

UL Listed

Y

CSA Certified

Y

ROHS Compatible

Compliant

UL Recognized

N

CULUS

N

Industry Standards

UL467,IEEE 837

Copper Tap Range

Conductor(s)
3/0 AWG-250 kcmil

Copper Stranded Run (Range)

250 kcmil-500 kcmil

Copper Solid Tap (Range)

N/A

Copper Solid Run Size (Range)

N/A

Type of Plating

Physical
Unplated

Connector Type

Tap

Plated (Yes or No)

N

Index Number

998

Product Material

Copper

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175