



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YGHC34C26  
7818102210688  
300-500 TO 6-2/0  
Active

**Web Use**  
BURNDY Product Line

**Dimensional**

B Length (in) 0.88  
Diameter (in) - Total 2.42

**General**

Product Description Copper Compression C Connector,  
300-500 kcmil, 3/4" Rod (Run) &  
6 AWG(Sol) - 2/0 AWG(Str) (Tap)

**Conductor(s)**

Copper Tap Range 7 AWG-2/0 AWG  
Copper Stranded Run (Range) 300 kcmil-500 kcmil  
Rod Size Run (Range) 3/4 in  
Copper Solid Tap (Range) 6 AWG-3/0 AWG  
Rebar Run Size (Range) N/A  
Copper Solid Run Size (Range) N/A

**Physical**

Type of Plating Unplated  
Connector Type Tap  
Plated (Yes or No) N  
Index Number 1011  
Product Material Copper

**Approvals / Certifications**

Rated for Direct Burial Y  
UL Listed Y  
CSA Certified Y  
ROHS Compatible Compliant  
Industry Standards UL468A-468B,UL467,IEEE 837

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175