



BURNDY Catalog Number
UPC Number
Description
Status

YAZ342NT38FX
 7818101660555
 350FX-LONG-OPEN-NARO TNG
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle
 Strip Length
 Length (in)
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 E - in

Straight
 2-5/16
 4.85
 Skived
 0.39
 Long
 0.23
 2.25
 0.96
 1.00

General

Number of Holes

 Product Description

2
 Cu Comp Terminal Flex Cond,
 Narrow Tongue/Bvl Entry, 2
 Hole/W/InspWindow, 373.7
 kcmil(925/#24) DLO, 350 kcmil
 Flex, 3/8" Stud, 1.00" Spacing ,
 Lng bbl

Conductor(s)

Copper Solid Size (Range)
 Navy Cable Size (Range)
 Copper Stranded (Range)

N/A
 N/A
 N/A

Physical

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Tin - Electro Plated
 3/8
 Blue
 Y
 19
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175