



BURNDY Catalog Number
UPC Number
Description
Status

YGHR29C34
 7818102207577
 4/0-250 TO 3/4 GRD ROD
 Active

Web Use
 BURNDY Product Line

Length (in)
 Height (in)
 B Length (in)
 B Length (Fraction)

Dimensional
 0.88
 2.19
 0.88
 22/25

Product Description
 Prefilled (Oxide Inhibitor)
 Type of Oxide Inhibitor

General
 Copper Compression Connector,
 4/0 AWG(Str)-250 kcmil, 3/4"
 Ground Rod
 Y
Other
 Penetrox E

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications
 Y
 Y
 Y
 Compliant
 N
 N
 UL467,IEEE 837

Copper Stranded (Range)

Conductor(s)
 4/0 AWG-250 kcmil

Type of Plating
 Connector Type
 Plated (Yes or No)
 Index Number
 Product Material

Physical
 Unplated
 Tap
 N
 998,1012
 Copper

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175