



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA28A5  
 7818107545044  
 4/0 AL 2-HOLE 1/2  
 Active

**Web Use**  
 BURNDY Product Line

#### Dimensional

|                     |          |
|---------------------|----------|
| Tongue Angle        | Straight |
| Strip Length        | 1-5/8    |
| Length (in)         | 5.19     |
| Tongue Type         | Standard |
| Bolt Hole Size (in) | 0.52     |
| Thickness           | 0.30     |
| B Length (in)       | 1.39     |
| Pad Width (in)      | 1.17     |
| E - in              | 1.75     |

#### General

|                     |                                                                                                                  |
|---------------------|------------------------------------------------------------------------------------------------------------------|
| Number of Holes     | 2                                                                                                                |
| Product Description | Aluminum Compression Lug, 2 Hole w/o Inspection Window, 4/0 AWG, 1/2" Stud, 1-3/4" Stud Hole Spacing, Tin Plated |

#### Conductor(s)

|                           |         |
|---------------------------|---------|
| Aluminum Size (Range)     | 4/0 AWG |
| Copper Solid Size (Range) | N/A     |
| Copper Stranded (Range)   | 4/0 AWG |

#### Physical

|                    |                      |
|--------------------|----------------------|
| Type of Plating    | Tin - Electro Plated |
| Bolt Hole Size     | 1/2                  |
| Color Code         | White                |
| Plated (Yes or No) | Y                    |
| Index Number       | 298                  |
| Product Material   | Aluminum             |

#### Approvals / Certifications

|                    |             |
|--------------------|-------------|
| UL Listed          | Y           |
| CSA Certified      | Y           |
| ROHS Compatible    | Compliant   |
| UL Recognized      | N           |
| CULUS              | N           |
| Industry Standards | UL468A-468B |

#### Documentation

For further technical assistance, please contact us

#### BURNDY LLC - USA

47 East Industrial Park Drive  
 Manchester NH 03109

#### BURNDY Technical Services

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175