



BURNDY Catalog Number
UPC Number
Description
Status

YA30LNT38
 7818100185522
 300,SHORT,3/8,NAR.TONG
 Active

Web Use
 BURNDY Product Line

Tongue Angle
 Length (in)
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 Strip Length

Dimensional

Straight
 2.97
 Chamfered
 0.39
 Standard
 0.16
 1.03
 0.96
 1-1/8

Number of Holes

General

1
 Copper Compression Lug, Narrow
 Tongue, 1 Hole w/ Inspection
 Window, 300 kcmil, 3/8" Stud,
 Short Barrel, Tin Plated

Product Description

Conductor(s)

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

N/A
 N/A
 N/A
 N/A
 N/A
 300 kcmil

Type of Plating
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin - Electro Plated
 White
 Y
 17
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175