



On Line Catalog



BURNDY Catalog Number	YA44L2NT38FX45
UPC Number	7818100804299
Description	750FLX-3/8X1-NARROW-45DG
Status	Active

Web Use
BURNDY Product Line

	Dimensional
Tongue Angle	45 Degree
Length (in)	4.71
Height (in)	1.50
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.33
B Length (in)	1.65
Pad Width (in)	1.63
E - in	1.00
Strip Length	1-5/8
	General
Number of Holes	2
	Cu Comp Terminal Flex Cond, 2
	Hole/W/InspWindow, 777.7
Product Description	kcmil(1925/#24)DLO, 750 kcmil
	FLEX, 600 V-35 kV, 3/8" Stud,
	1.00" Spacing, 45 Deg Bent, Std
	bbl
	Conductor(s)
Flex (Class G) Size - Range	750
Flex (Class H) Size - Range	750
Flex (Class I) Size - Range	750
Copper Solid Size (Range)	N/A
DLO Size (Range)	777.7 (1925/#24)
Copper Stranded (Range)	750
	Physical
Type of Plating	Tin
Bolt Hole Size	3/8
Color Code	Yellow
Plated (Yes or No)	Y
Index Number	L115
Product Material	Copper
	Approvals / Certifications
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175