



BURNDY Catalog Number
UPC Number

YAV14
7818100248366
20-14 HVYDTY RING 8-10 S,0.78
IN L
Active

Description
Status

Web Use
BURNDY Product Line

Length (in)
Tongue Type
Stud Size (in)
Pad Width (in)

Dimensional
0.79
Ring
#10,#8
0.29

Product Description

General
Copper Compression Lug, Ring
Tongue w/ Inspection Hole, 1
Hole, 20-14 AWG/20-12 AWG, #8-
#10 Stud, Short Barrel, Tin Plated

Aircraft Cable Size (Range)
Copper Solid Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)

Conductor(s)
N/A
20 -14 AWG
N/A
20 AWG-14 AWG

Type of Plating
Connector Type
Plated (Yes or No)

Physical
Tin - Electro Plated
Terminal - Ring
Y

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Approvals / Certifications
Y
Y
Compliant
N
N
UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175