



BURNDY Catalog Number
UPC Number
Description
Status

YAV28TC38FXB
 7818100808322
 BELLED HYLUG-4/0 FLEX-3/
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	3.19
Tongue Type	Standard
Barrell Style	Belled
Bolt Hole Size (in)	0.39
Barrel Type	Long
Thickness	0.14
B Length (in)	1.77
Pad Width (in)	1.14
Strip Length	1-7/8

General

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/o Inspection Window, 4/0 AWG / 250 FLEX, 3/8" Stud, Long Barrel, Belled End, Tin Plated

Conductor(s)

Aircraft Cable Size (Range)	N/A
Flex (Class H) Size - Range	4/0 AWG
Flex (Class I) Size - Range	4/0 AWG
Copper Solid Size (Range)	N/A
DLO Size (Range)	4/0 (550/#24) DLO
Navy Cable Size (Range)	200 (61) Navy
Copper Stranded (Range)	4/0 AWG
Flex (Class G) Size - Range	1/0 AWG
Flex (Class M) Size - Range	4/0 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Yellow
Plated (Yes or No)	Y
Index Number	16
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175

