



BURNDY Catalog Number
UPC Number
Description
Status

YAV4CLTC38FX
 7818100226277
 4FLEX 3/8STUD
 Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	1.67
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Standard
Thickness	0.08
B Length (in)	0.50
Pad Width (in)	0.58
Strip Length	1/2

General

Number of Holes	1
Product Description	Copper Compression Lug, 1 Hole w/ Inspection Window, 4 Flex, 3/8" Stud, Short Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range	4 AWG
Flex (Class H) Size - Range	4 AWG
Flex (Class I) Size - Range	4 AWG
Copper Solid Size (Range)	4 AWG
DLO Size (Range)	5 (91/#24) DLO-4 (105/#24) DLO
Copper Stranded (Range)	4 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Gray
Plated (Yes or No)	Y
Index Number	8
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175