



BURNDY Catalog Number
UPC Number

Description
Status

YAZ25TC12
7818102399199
CULUG-1/0AWG-LONG W/PORT-
1/2" STUD
Active

Web Use
BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	2.84
Barrell Style	Skived
Bolt Hole Size (in)	0.52
Barrel Type	Long
Thickness	0.12
B Length (in)	1.38
Pad Width (in)	0.75
Strip Length	1-7/16

General

Number of Holes	1
Product Description	Cu Tubing Hylug (One Hole Code), 1 Hole with Inspection Window, 1/0 AWG Code, 100 Navy, 600V- 35kV, 1/2" stud, Long, Compression, 0.52 in BCD, Pink

Conductor(s)

Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	100 (61) Navy
Copper Stranded (Range)	1/0

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Pink
Plated (Yes or No)	Y
Index Number	12,348
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175